





U  
建築汎用品

## ラバー製手すりシステム



Technical drawing of the mounting bracket for the 12-inch model. The drawing shows the bracket's profile and its installation into a concrete wall. Key dimensions include a total width of 80mm, a mounting hole offset of 59mm, a bracket body width of 42mm, and a mounting hole offset of 38mm. The bracket is secured with a bolt and nut. The mounting hole is 8mm in diameter. The bracket is shown installed into a concrete wall, with dimensions indicating the depth of the hole (87.5mm) and the total depth of the bracket (113.5mm). The bracket is labeled with a circled '12'.



- 握力が弱いお年よりやお身体の不自由な方が移動の手段として手すりを使用される場合、握るだけでなく、身体を手すりにもたせかけて支えながら移動をされています。この点を踏まえ、誰でも安全に身体を支え、移動できるように開発した手すりです。
- 手すりの表面は合成ゴムで覆っているためスベリを防止し、体の一部をぶつけても効果的に衝撃を吸収します。また、手ざわりもソフトで冷たくないため、寒冷地などでの使用にも適しています。
- 握りやすさはもちろん、身体を手すりにもたせかけて支えながら移動するといった使用方法でも使い勝手の良い、たまご形の断面形状を採用しています。体重を支える時に手に受ける負担が軽くなるように考えています。
- とくにリウマチの方には最適です。
- 廊下から階段まで連続設置ができ、手すりが途中で途切れる心配がありません。
- 老化、オゾン劣化に優れた合成ゴムを使用しています。長期間きれいな状態でご使用いただけます。
- 手すり上面に貼る蓄光テープもご用意できます。一定時間蛍光灯や太陽光線などの光に照らされた時に、暗闇で発光が確認できるテープです。弊社営業担当者までお問い合わせください。
- ユニバーサルデザインの観点から建築設備機器を評価した、国土交通省発行の「移動円滑化建築設備等選定提案集」に選定掲載されています。
- 優良住宅部品（BL部品）として2000年8月末から2010年3月末まで認定を受けた製品です。

施工の際は、製品に付属の取付説明書をよく読んでから作業を始めてください。

ホームページアドレス <http://www.sugatsune.co.jp/>  
No.200-3カタログ  
20120501